


Setting the standard for panel mounting

PS-SR225S & PS-SR225SS Seismount – 225mm

PS-SR225S	USE WITH:	INSTALL WITH:
PS-SR225SS	PC Standard Range, LP Low Profile Range, VL Very Low Profile Range, MC Metal Range	M10 pan head screw 6.3 x 8mm euro screw

INSTALLATION STEPS FOR CEILINGS



info@fastmount.com

*Specification subject to change without notice, see website for updates. Copyright © Fastmount Ltd. www.fastmount.com

INSTALLATION GUIDE PS-SR225S(S) / DATE 1018



Setting the standard for panel mounting

PS-SR225S & PS-SR225SS Seismount - 225mm

PS-SR225S	USE WITH: PC Standard Range, LP Low Profile Range, VL Very Low Profile Range, MC Metal Range	INSTALL WITH: M10 pan head screw 6.3 x 8mm euro screw
INSTALLATION STEPS FOR WALLS	2 Partially screw M10 pan-head screw into substrate Wall PC-F1A female clip	PC-M1B
 Screw folded end of PS- SR225S onto panel with 1 x 6.3 x 8mm Euro screw plus 2 x M8 pan-head screws Panel PS-SR225S note: length of screws to suit panel thickness 	 Slot the PS-SR225S onto pan-head screw on substrate and tighten screw Panel Value PC-F1A Value P	substrate

info@fastmount.com

www.fastmount.com

*Specification subject to change without notice, see website for updates. Copyright © Fastmount Ltd. INSTALLATION GUIDE PS-SR225S(S) / DATE 1018 PROUDLY DESIGNED & MANUFACTURED IN NEW ZEALAND